

VM016

Enclosure, Design30, 16 module, with DIN rail, metal

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	100 A
---------------	-------

Dimensions

Depth of installed product	102 mm
----------------------------	--------

Height of installed product	240 mm
-----------------------------	--------

Width of installed product	364 mm
----------------------------	--------

Capacity

Number of modules	16
-------------------	----

Cover, door

Type of door closing	non keylock
----------------------	-------------

Door locking	without
--------------	---------

Interlockable	No
---------------	----

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel

Equipment

Number of rows	1
Can be accessorized	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
Protection class	Protection class III