

VM018

Enclosure, Design30, 18 module, with DIN rail, metal

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|----------------------------|--------|
| Depth of installed product | 102 mm |
|----------------------------|--------|

| | |
|-----------------------------|--------|
| Height of installed product | 240 mm |
|-----------------------------|--------|

| | |
|----------------------------|--------|
| Width of installed product | 471 mm |
|----------------------------|--------|

Capacity

| | |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

Cover, door

| | |
|----------------------|-------------|
| Type of door closing | non keylock |
|----------------------|-------------|

| | |
|--------------|---------|
| Door locking | without |
|--------------|---------|

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Materials

| | |
|-------------------|-----------------------|
| Colour | pure white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| RAL colour number | 9010 |
| Material | Steel |

Equipment

| | |
|---------------------|----|
| Number of rows | 1 |
| Can be accessorized | No |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|----------------------|
| Protection index IP | IP2XC |
| Protection class | Protection class III |