



BD263

Technical characteristics

Architecture

Neutral position	left
Number of poles	2 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
--------------------------	-------

Electric current

Rated residual operating current	30 mA
----------------------------------	-------

Power

Total power loss under IN	4.4 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
---	-------------------

Safety

Residual current type	HI
-----------------------	----