



BD263

## Technical characteristics

### Architecture

Neutral position	left
Number of poles	2 P

### Main electrical features

Rated operational voltage U <sub>e</sub>	230 / 400 V
Frequency	50 Hz

### Voltage

Rated insulation voltage	500 V
--------------------------	-------

### Electric current

Rated residual operating current	30 mA
----------------------------------	-------

### Power

Total power loss under I <sub>N</sub>	4.4 W
---------------------------------------	-------

### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
-------------------------------------------	-------------------

### Safety

Residual current type	HI
-----------------------	----