



BD263

## Technical characteristics

### Architecture

Neutral position	left
Number of poles	2 P

### Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

### Voltage

Rated insulation voltage	500 V
--------------------------	-------

### Electric current

Rated residual operating current	30 mA
----------------------------------	-------

### Power

Total power loss under IN	4.4 W
---------------------------	-------

### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>

### Safety

Residual current type	HI
-----------------------	----