



BE163T

**Earth leakage add-on-block 3P 63A 100mA A Class 1mod Electronic**

**Technical Characteristics**

Neutral position	right
Number of poles	3 P
Rated operational voltage Ue	240 / 415 V
Frequency	50 Hz
Rated current	63 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V
Rated residual operating current	100 mA
Total power loss under I <sub>N</sub>	3.2 W
Short-time delayed tripping	No
Electric endurance in number of cycles	1000
Number of mechanical operations	1000
Number of modules	1
Tightening torque	3,5Nm
Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	A
Operating temperature	-5...40 °C