



BF163T

Earth leakage add-on-block 3P 63A 300mA A Class 1mod Electronic

Technical characteristics

Architecture

Neutral position	right
Number of poles	3 P

Main electrical features

Rated operational voltage Ue	240 / 415 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Power

Total power loss under IN	3.2 W
---------------------------	-------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	3,5Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²

Safety

Residual current type	A
-----------------------	---

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------