



BF163T

Earth leakage add-on-block 3P 63A 300mA A Class 1mod Electronic

Technical characteristics

Architecture

Neutral position	right
Number of poles	3 P

Main electrical features

Rated operational voltage U _e	240 / 415 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Power

Total power loss under I _N	3.2 W
---------------------------------------	-------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	3,5Nm
-------------------	-------

Safety

Protection index IP	IP20
Residual current type	A

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------