



BF464

## Earth leakage add-on block 4P 63A 300mA AC Class

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	4 P

#### Main electrical features

Rated operational voltage U <sub>e</sub>	230 / 400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	300 mA
----------------------------------	--------

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Power

Total power loss under I <sub>N</sub>	35.5 W
---------------------------------------	--------

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

#### Connection

Type of connection	with screw
--------------------	------------

#### Safety

Protection index IP	IP20
Residual current type	AC

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------