



BN464

## Earth leakage add-on block 4P 63A 100mA AC S Class

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	4 P

#### Main electrical features

Rated operational voltage U <sub>e</sub>	230 / 400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	100 mA
----------------------------------	--------

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
---	-------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
Residual current type	AC SEL

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------