



BP264

**Earth leakage add-on block 2P 63A 300mA AC S Class**

**Technical characteristics**

**Architecture**

Neutral position	left
Number of poles	2 P
Type of pole	2 P

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	300 mA
----------------------------------	--------

**Dimensions**

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

**Power**

Total power loss under IN	4.4 W
---------------------------	-------

**Tripping**

Short-time delayed tripping	Yes
-----------------------------	-----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

**Installation, mounting**

Tightening torque	2,8Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>

**Safety**

Residual current type	AC SEL
-----------------------	--------

**Use conditions**

