



BTC380E

:hager

Earth leakage add-on-block 3P 125A Adjustable type AC

Technical Characteristics

Neutral position	Left or right
Number of poles	3 P
Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz
Rated current	125 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Rated residual operating current	300 mA / 500 mA / 1 A
Rating current 30°C	125 A
Depth of installed product	69 mm
Height of installed product	103 mm
Width of installed product	187 mm
Total power loss under IN	11.25 W
Short-time delayed tripping	No
Electric endurance in number of cycles	1000
Number of mechanical operations	7000
Number of modules	6
Tightening torque	3,5Nm
Connection cross-sect. flexible conductor	10 - 50 mm ²
Connection cross-sect. rigid cable	10 / 70 mm ²
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	AC