



CD284U

**RCCB 2P 100A 30mA AC**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P

**Main electrical features**

Frequency	50 Hz
-----------	-------

**Electric current**

Rated residual operating current	30 mA
Rated conditional short-circuit current $I_{nc}$ according to EN 61008-1	6 kA

**Electric current / temperature**

Rating current 30°C	100 A
---------------------	-------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under $I_N$	14.3 W
------------------------------	--------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

**Standards**

Standard text	EN 61008-1
European directive WEEE	concerned

**Safety**

Residual current type	AC
-----------------------	----

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------