



CE285J

**RCCB 2P 100A 100mA A Class**

**Technical Characteristics**

Neutral position	right
Number of poles	2 P
Fixing mode	Din-Rail
Frequency	50 Hz
Rated current	100 A
Rated residual operating current	100 mA
Breaking and opening capacity	1.5 kA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA
Rating current 30°C	100 A
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm
Total power loss under IN	14.3 W
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Number of modules	2
Type of connection	with screw
Standard text	IEC 61008-1
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	A
Operating temperature	-25...40 °C