



CF484U

RCCB 4P 100A 300mA AC Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	4 P

Main electrical features

Frequency	50 Hz
-----------	-------

Electric current

Rated residual operating current	300 mA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

Electric current / temperature

Rating current 30°C	100 A
---------------------	-------

Dimensions

Depth of installed product	70 mm
Height of installed product	86 mm
Width of installed product	70 mm

Power

Total power loss under IN	30.2 W
---------------------------	--------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Connection

Type of connection	with screw
--------------------	------------

Standards

Standard text	EN 61008-1
---------------	------------

Safety

Protection index IP	IP20
Residual current type	AC

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------