



CF484U

**RCCB 4P 100A 300mA AC Class**

**Technical Characteristics**

Neutral position	right
Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)
Frequency	50 Hz
Rated current	100 A
Rated residual operating current	300 mA
Breaking and opening capacity	1.5 kA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA
Rating current 30°C	100 A
Depth of installed product	70 mm
Height of installed product	86 mm
Width of installed product	70 mm
Total power loss under IN	30.2 W
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Number of modules	4
Type of connection	with screw
Standard text	EN 61008-1
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	AC
Operating temperature	-25...40 °C