



CR64AX/1.0PVC/2

**CR64AX c/w 4 Core 1mm<sup>2</sup> 2m PVC Lead**

**Technical characteristics**

**Main electrical features**

|  |                   |
|--|-------------------|
| Rated operational voltage U <sub>e</sub> | 207 / 230 / 253 V |
|--|-------------------|

**Materials**

|        |            |
|--------|------------|
| Colour | pure white |
|--------|------------|

**Connection**

|           |                                 |
|-----------|---------------------------------|
| Cable End | Prepared - end of barrel closed |
|-----------|---------------------------------|

**Cable**

|                |                   |
|----------------|-------------------|
| Conductor Size | 1 mm <sup>2</sup> |
| Cable Standard | BS 6141           |

**Equipment**

|                                 |                 |
|---------------------------------|-----------------|
| Number of terminations -sockets | 5               |
| Number of terminations -plugs   | 4               |
| Contact Material                | Phosphor Bronze |

**Use**

|                 |              |
|-----------------|--------------|
| Mechanical Load | 5 Kg maximum |
|-----------------|--------------|

**Safety**

|                |          |
|----------------|----------|
| Inflammability | UL 94 V0 |
|----------------|----------|