



CZ001

Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC

Technical characteristics

Electric current

Rated current	6 A
---------------	-----

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Capacity

Number of modules	1
-------------------	---

Connection

Cross-section flexible conductor	4 mm ²
----------------------------------	-------------------

Cross-section rigid conductor	6 mm ²
-------------------------------	-------------------

Voltage

Rated insulation voltage U _i	500 V
---	-------

Type voltage supply	AC
---------------------	----

Frequency

Frequency	50 - 50 Hz
-----------	------------

Endurance

Number of mechanical operations	12,000
---------------------------------	--------

Electric endurance in number of cycles	6,000
--	-------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Power

Total power loss under I _N	0.10 W
---------------------------------------	--------

Dimensions

Width	18 mm
-------	-------

Equipment

Number of INV contacts	0
------------------------	---

Number of NC contacts	1
-----------------------	---