



CZ001

Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 / 440 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
--------------------------	-------

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Dimensions

Width of installed product	18 mm
----------------------------	-------

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²
Type of connection	with screw
Type of contacts	auxiliary contact 1NC+1NO alarm contact 1NC+1NO

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------