



EC050

Single phase KWHmeter direct 32A 1M

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	1P+N

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4 kV
--------------------------	------

Power

Power consumed	6.7 VA
Total power loss under IN	6.7 W

Measurement

Type of measuring instrument	electrical
------------------------------	------------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
---	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------