



EC051

## Single phase KWHmeter direct 32A 1M with pulsed output

### Technical characteristics

#### Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

#### Main electrical features

Rated operational voltage Ue	185 / 230 / 275 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4 kV
--------------------------	------

#### Dimensions

Width of installed product	17.5 mm
----------------------------	---------

#### Power

Power consumed	6.7 VA
Total power loss under IN	6.7 W

#### Measurement

Type of measuring instrument	electronical
------------------------------	--------------

#### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
-------------------------------------------	----------------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------