



EC051

Single phase KWHmeter direct 32A 1M with pulsed output

Technical characteristics

Architecture

Type of pole 1P+N

Main electrical features

Rated operational voltage Ue 185 / 230 / 275 V

Frequency 50 Hz

Voltage

Rated insulation voltage 4 kV

Dimensions

Width of installed product 17.5 mm

Power

Power consumed 6.7 VA

Total power loss under IN 6.7 W

Measurement

Type of measuring instrument electrical

Connection

Connection cross-sect. flexible conductor 1 / 4mm²

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...45 °C