

Busbar, Cable



EC12160CT

## Current Transformer with RJ45 output BGUK 3-Phase 160A/330mV Class 1 pitch 25mm

## **Technical characteristics**

Filter Type product	3-phase current transformer replacement
Functions	
Accuracy class	1
Dimensions	
Height	80 mm
Width	76 mm
Depth	76 mm
Height of opening	15 mm
Width of opening	30 mm
Connectivity	
Type of connection	Plug-in connection
Frequency	
Frequency	50 - 50 Hz
Voltage	
Rated insulation voltage Ui	3,000 V
Use conditions	
Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C
Electric current	
Max. intensity of primary	160 A
Installation, mounting	

Mounting on