



EC1260CT

**Current Transformer with RJ45 output BGUK 3-Phase 60A/330mV Class 1 pitch 25mm**

**Technical characteristics**

**Functions**

Accuracy class	1
----------------	---

**Dimensions**

Height	80 mm
Width	76 mm
Depth	76 mm
Height of opening	15 mm
Width of opening	30 mm

**Connectivity**

Type of connection	Plug-in connection
--------------------	--------------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Rated insulation voltage $U_i$	3,000 V
--------------------------------	---------

**Use conditions**

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C

**Electric current**

Max. intensity of primary	60 A
---------------------------	------

**Installation, mounting**

Mounting on	Busbar, Cable
-------------	---------------