



EC152

## 1Ph Kwhmeter direct 63A double tarif

### Technical characteristics

#### Architecture

Number of poles	1 P
Type of pole	1P+N

#### Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	4 kV
--------------------------	------

#### Dimensions

Height of installed product	90 mm
Width of installed product	52.5 mm

#### Power

Power consumed	1.3 VA
Total power loss under IN	0.2 W

#### Measurement

Type of measuring instrument	electronical
------------------------------	--------------

#### Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

#### Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 16mm <sup>2</sup>

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------