



EC154M

1Ph Kwhmeter direct 63A with MID approval

Technical characteristics

Architecture

Number of poles	1 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	6 kV
--------------------------	------

Dimensions

Height of installed product	90 mm
Width of installed product	52.5 mm

Power

Power consumed	1.3 VA
Total power loss under IN	0.2 W

Measurement

Type of measuring instrument	electronical
------------------------------	--------------

Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
---	-----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------