



EC25250CT

Current Transformer with RJ45 output BGUK 3-Phase 250A/330mV Class 1 pitch 35mm

Technical characteristics

Specific identification attributes for Protection

Filter Type product 3-phase current transformer replacement

Functions

Accuracy class 1

Dimensions

Height 80 mm

Width 105 mm

Depth 54 mm

Height of opening 25 mm

Width of opening 21 mm

Connectivity

Type of connection Plug-in connection

Frequency

Frequency 50 - 50 Hz

Voltage

Rated insulation voltage U_i 3,000 V

Use conditions

Operating temperature -25 - 50 °C

Storage/transport temperature -40 - 85 °C

Electric current

Max. intensity of primary 250 A

Installation, mounting

Mounting on Busbar, Cable