



EC365B

### 3Ph Kwhmeter direct 100A bi-directionnal

#### Technical characteristics

##### Architecture

Number of poles	3 P
Type of pole	3P+N

##### Main electrical features

Rated operational voltage Ue	195 / 400 / 460 V
Frequency	50/60 Hz

##### Dimensions

Height of installed product	90 mm
-----------------------------	-------

##### Power

Power consumed	7.5 VA
Total power loss under IN	1.8 W

##### Measurement

Type of measuring instrument	electronical
------------------------------	--------------

##### Power supply

Supply voltage	230/400 V +/- 15%
----------------	-------------------

##### Connection

Connection cross-sect. flexible conductor	2,5 / 35mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5 / 35mm <sup>2</sup>

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------