



EC365B

3Ph Kwhmeter direct 100A bi-directionnal

Technical Characteristics

Type of pole	3P+N
Fixing mode	REG
Rated operational voltage Ue	195 / 400 / 460 V
Frequency	50/60 Hz
Rated current	100 A
Height of installed product	90 mm
Power consumed	7.5 VA
Total power loss under IN	1.8 W
Type of measuring instrument	electronical
Number of modules	7
Supply voltage	230/400 V +/- 15%
Connection cross-sect. flexible conductor	2,5 / 35mm ²
Connection cross-sect. rigid cable	2,5 / 35mm ²
Protection index IP	IP20
Operating temperature	-10...55 °C