



EC40630CT

**Current Transformer with RJ45 output BGUK 3-Phase 630A/330mV Class 1 pitch 45mm**

**Technical characteristics**

**Specific identification attributes for Protection**

Filter Type product 3-phase current transformer replacement

**Functions**

Accuracy class 1

**Dimensions**

Height 90 mm

Width 140 mm

Depth 54 mm

Height of opening 31 mm

Width of opening 31 mm

**Connectivity**

Type of connection Plug-in connection

**Frequency**

Frequency 50 - 50 Hz

**Voltage**

Rated insulation voltage  $U_i$  3,000 V

**Use conditions**

Operating temperature -25 - 50 °C

Storage/transport temperature -40 - 85 °C

**Electric current**

Max. intensity of primary 630 A

**Installation, mounting**

Mounting on Busbar, Cable