



EE600



IP55



LED Floodlight with PIR 220 / 360° , white

Technical characteristics

Architecture

Fixing mode	Screwed
-------------	---------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V AC
-------------------	----------

Power

Halogen switching capacity 230V	410 W
---------------------------------	-------

Incandescent bulb power	300 W
-------------------------	-------

Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Lumen	3400 lm
-------	---------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection

Connection type	1 to 1,5 mm ²
-----------------	--------------------------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-20...40 °C
-----------------------	-------------