



EE600



**IP55**

## LED Floodlight with PIR 220 / 360° , white

### Technical characteristics

#### Architecture

Fixing mode Screwed

#### Main electrical features

Frequency 50/60 Hz

#### Voltage

Operating voltage 230 V AC

#### Power

Halogen switching capacity 230V 410 W

Incandescent bulb power 300 W

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

#### Lighting control

Brightness measurement range 5 / 1000 Lux

Lumen 3400 lm

#### Installation, mounting

Maximum Mounting Height 4 m

#### Connection

Connection type 1 to 1,5 mm<sup>2</sup>

#### Safety

Protection class isol.class II

#### Use conditions

Operating temperature -20...40 °C