



EE804A



Movement detector 360° surface mounted with normally open contact

Technical characteristics

Detection

Detection angle	360 - 360
Type of sensor	Movement detector, Presence detector

Settings

Time delay	5 S - 30 Min
------------	--------------

Lighting

Response brightness adjustable	5 - 1,000 lx
--------------------------------	--------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	105.50 mm
Built-in depth	0
Recommended installation height	2.5 - 3.5 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	White
Material	Plastic

Safety

Ingress Protection (IP) class	IP21
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Texts

Function	Can only be used as individual unit
Installation mode	Installation possible on flush-mounted box, For ceiling mounting
Type of connection	With screw terminals