




EE804A



IP21

Movement detector 360° surface mounted with normally open contact

Technical characteristics

Architecture

Bus system Without

Functions

Function can only be used as individual unit

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

Dimensions

Height of installed product 50 mm

Width of installed product 105.5 mm

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 360 °

Materials

Colour white

Material plastic

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Mounting type surface-mounted

Maximum Mounting Height 4 m

Connection

Number of contacts 1

Type of connection with screw terminals

Settings

Setting with potentiometers for setting the response brightness and delay time without dismantling

Scope of delivery

Component with fitting material

Equipment

Angle of horizontal detection

360 °

Safety

Protection class

isol.class II

Use conditions

Operating temperature

-5...45 °C