



Presence detector 360°, 1 channel, wall mounted, white

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Height of installed product	31 mm
Width of installed product	100 mm

Power supply

Supply voltage	230 V
----------------	-------

Detection

Detection angle	360 °
-----------------	-------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	plastic

Lighting control

Brightness measurement range	5 / 1200 Lux
------------------------------	--------------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Equipment

Angle of horizontal detection	360 °
-------------------------------	-------

Safety

Protection index IP	IP41
Protection class	isol.class II

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------