




EE810



Presence detector 360°, 1 channel, wall mounted, white

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Height of installed product 31 mm

Width of installed product 100 mm

Power supply

Supply voltage 230 V

Detection

Detection angle 360 °

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Brightness measurement range 5 / 1200 Lux

Installation, mounting

Maximum Mounting Height 4 m

Equipment

Angle of horizontal detection 360 °

Safety

Protection class isol.class II

Use conditions

Operating temperature 0...45 °C