



EE810

μ IP41 



**Presence detector 360°, 1 channel, wall mounted, white**

**Technical characteristics**

**Architecture**

Bus system Without

**Functions**

Function with communication between individual units connected in parallel (controller system formation)

**Main electrical features**

Rated operational voltage Ue 230 V

Frequency 50 Hz

**Dimensions**

Height of installed product 31 mm

Width of installed product 100 mm

**Reach distance**

Max. transmission range 12m

**Power supply**

Supply voltage 230 V

**Detection**

Detection angle 360 °

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

**Lighting control**

Brightness measurement range 5 / 1200 Lux

**Installation, mounting**

Maximum Mounting Height 4 m

**Scope of delivery**

Component with flush-mounted switch insert

**Equipment**

Angle of horizontal detection 360 °

**Safety**

Protection class isol.class II

**Use conditions**

---

Operating temperature

0...45 °C