



Presence detector 360°, 1 channel, wall mounted, white

Technical characteristics

Architecture

Bus system	Without
------------	---------

Functions

Function	with communication between individual units connected in parallel (controller system formation)
----------	---

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz

Dimensions

Height of installed product	31 mm
Width of installed product	100 mm

Reach distance

Max. transmission range	12m
-------------------------	-----

Power supply

Supply voltage	230 V
----------------	-------

Detection

Detection angle	360 °
-----------------	-------

Materials

Colour	pure white
Type of surface treatment	Untreated

Lighting control

Brightness measurement range	5 / 1200 Lux
------------------------------	--------------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Scope of delivery

Component	with flush-mounted switch insert
-----------	----------------------------------

Equipment

Angle of horizontal detection	360 °
-------------------------------	-------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature

0...45 °C