



EE811

IP41



Presence detector 360°, 2 channels, flush mounted, white

Technical characteristics

Architecture

Bus system Without

Functions

Function Linking with 1-channel presence detectors in order to expand the detection area

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50 Hz

Dimensions

Width of installed product 100 mm

Reach distance

Max. transmission range 12m

Power supply

Supply voltage 230 V

Detection

Detection angle 360 °

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Brightness measurement range 5 / 1200 Lux

Installation, mounting

Maximum Mounting Height 4 m

Scope of delivery

Component with flush-mounted switch insert

Equipment

Angle of horizontal detection 360 °

Safety

Protection class isol.class II

Use conditions

Operating temperature

0...45 °C