



EE860



**IP55**



## Motion detector comfort 220°, IP55, wall mounted, blanc

### Technical characteristics

#### Architecture

Fixing mode surface-mounting

#### Main electrical features

Frequency 50/60 Hz

#### Dimensions

Height of installed product 2.5 m

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 220 °

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

#### Lighting control

Brightness measurement range 5 / 1000 Lux

#### Installation, mounting

Maximum Mounting Height 4 m

#### Connection

Type of connection with screw terminals

#### Scope of delivery

Component with fitting material

#### Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

#### Safety

Protection index IP IP55

#### Use conditions

Operating temperature -20...55 °C