



EE860



## Motion detector comfort 220°, IP55, wall mounted, blanc

### Technical characteristics

#### Detection

Detection angle	220 - 220
Type of sensor	Movement detector

#### Settings

Time delay	5 S - 30 Min
------------	--------------

#### Lighting

Response brightness adjustable	5 - 1,000 lx
--------------------------------	--------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Dimensions

Width	91 mm
Built-in depth	0
Recommended installation height	2.50 - 2.50 m

#### Use conditions

Operating temperature	-20 - 55 °C
-----------------------	-------------

#### Materials

Colour	White
Material	Plastic

#### Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

#### Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

#### Texts

Function	Presence simulation, Can be used as a single unit, main device or extension unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With screw terminals