



EE860



Motion detector comfort 220°, IP55, wall mounted, blanc

Technical characteristics

Architecture

Bus system Without

Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 220 °

Materials

Colour white

Type of surface treatment Untreated

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Settings

Setting with potentiometers for setting the response brightness and delay time without dismantling

Scope of delivery

Component with fitting material

Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

Use conditions

Operating temperature -20...55 °C