



EE883



Circulation sensor HF

Technical characteristics

Detection

Detection angle	360 - 360
Type of sensor	Movement detector

Settings

Time delay	5 S - 15 Min
------------	--------------

Lighting

Response brightness adjustable	2 - 1,000 lx
--------------------------------	--------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Dimensions

Recommended installation height	2.50 - 2.50 m
---------------------------------	---------------

Use conditions

Operating temperature	-20 - 50 °C
-----------------------	-------------

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS), Polycarbonate (PC)
----------	---

Safety

Ingress Protection (IP) class	IP54
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Texts

Function	Parallel connection of several detectors in order to expand the detection area
Installation mode	For ceiling mounting