



EE960

Emergency light

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated voltage	230 V

Dimensions

Depth of installed product	51 mm
Height of installed product	70 mm
Width of installed product	54 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Power supply

Supply voltage	230 V
----------------	-------

Materials

Material	plastic
----------	---------

Incandescent bulbs control

Max. power with incandescent lamps	1 W
------------------------------------	-----

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	Clamp/screw mounting

Use conditions

Operating temperature	0...40 °C
-----------------------	-----------