



EE960

Emergency light

Technical characteristics

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz
Rated voltage	230 V

Dimensions

Depth of installed product	51 mm
Height of installed product	70 mm
Width of installed product	54 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Power supply

Supply voltage	230 V
----------------	-------

Materials

Material	plastic
----------	---------

Incandescent bulbs control

Max. power with incandescent lamps	1 W
------------------------------------	-----

Connection

Type of connection	Clamp/screw mounting
--------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...40 °C
-----------------------	-----------