



EG100

## 1 channel weekly programmer

### Technical characteristics

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

#### Power

Power consumed	4 VA
Total power loss under IN	4 W

#### Battery

Power reserve [years]	99 a
Charging time of the power reserve in hours	0

#### Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Number of contacts	1
Type of contacts	1 changeover

#### Settings

Summer / Winter time change	manual
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

#### Equipment

Number of channels	1
Supply failure reserve	programming unlimited

#### Use

Cycle	weekly
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Working accuracy	5