



EG403E



Weekly time switch 4 channels, digital, 4 modules

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	69 mm
Height of installed product	90 mm
Width of installed product	71 mm

Power

Power consumed	2 VA
Total power loss under IN	2 W

Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Incandescent bulbs control

Max. power with incandescent lamps	1500 W
------------------------------------	--------

Connection

Type of connection	quick connect
Number of contacts	4

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital, with programming key
Programming cycle	4X7D

Equipment

Number of channels	4
Supply failure reserve	5 years

Use

Cycle	weekly
-------	--------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...50 °C
Working accuracy	+ 0,2 s / 24h