



EGN200

Multi-function time switch 2 channels bluetooth

Technical characteristics

Architecture

Fixing mode DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

Nominal voltage 230 V

Type of supply voltage AC

Voltage

Operating voltage 230 V AC

Dimensions

Depth of installed product 61.6 mm

Height of installed product 90 mm

Width of installed product 35.8 mm

Power

Power consumed 0.6 VA

Power consumption (operation) 350 mW

Lighting control

Brightness measurement range 1 / 2000 Lux

Fluorescent bulbs control

Max. power with fluorescent parallel lamps 400 W

Max. power fluo. duo lamp comp. series 1000 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Number of contacts 2

Type of contacts 1 changeover

Type of connection with screw terminal

Settings

Shortest switching time 1 mn

Equipment

Number of channels 2

Supply failure reserve

10 years

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Working accuracy

60