



EGN200

Multi-function time switch 2 channels bluetooth

Technical characteristics

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Nominal voltage	230 V
Type of supply voltage	AC

Voltage

Operating voltage	230 V AC
-------------------	----------

Dimensions

Depth of installed product	61.6 mm
Height of installed product	90 mm
Width of installed product	35.8 mm

Power

Power consumed	0.6 VA
Power consumption (operation)	350 mW

Lighting control

Brightness measurement range	1 / 2000 Lux
------------------------------	--------------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	400 W
Max. power fluo. duo lamp comp. series	1000 W

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Number of contacts	2
Type of contacts	1 changeover
Type of connection	with screw terminal

Settings

Shortest switching time	1 mn
-------------------------	------

Equipment

Number of channels	2
--------------------	---

Supply failure reserve	10 years
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Working accuracy	60