



EGN400

## Multi-function time switch 4 channels bluetooth

### Technical characteristics

#### Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Nominal voltage	230 V
Type of supply voltage	AC

#### Dimensions

Depth of installed product	61.6 mm
Height of installed product	90 mm
Width of installed product	70 mm

#### Power

Power consumed	0.71 VA
Power consumption (operation)	500 mW

#### Lighting control

Brightness measurement range	1 / 2000 Lux
------------------------------	--------------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	400 W
Max. power fluo. duo lamp comp. series	1000 W

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	0.5Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0.2 / 2.5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,2 / 4mm <sup>2</sup>
Type of connection	with screw
Number of contacts	4
Type of contacts	1 changeover
Type of connection	with screw terminal

#### Settings

Shortest switching time	1 mn
-------------------------	------

**Equipment**

Type of programmable thermostat	Digital
Number of channels	4
Supply failure reserve	10 years

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Working accuracy	60
------------------	----